

## PolySwitch® PTC Devices

**Overcurrent Protection Device** 

**PRODUCT: AHS120** 

DOCUMENT: SCD28207

REV LETTER: B

REV DATE: JULY 26, 2016

PAGE NO.: 1 OF 2


### **Specification Status: Released**


Maximum Electrical Rating
Operating Voltage / Interrupt Current
16Vpc / 50A

Marking:

H12 — Part Identification
— Manufacturer's Mark

□□□□ - Lot Identification





#### Notes:

- 1. All metal surfaces are tin plated.
- 2. Drawing not to scale.

#### **TABLE I. DIMENSIONS:**

	Α		В		С		D		Е		F		G		Н
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
mm:	6.73	7.98		3.00	4.8	5.44	0.56	0.71	0.56	0.71	2.16	2.41	0.66	1.37	0.43
in*:	(0.265)	(0.314)	I	(0.118)	(0.19)	(0.214)	(0.022)	(0.028)	(0.022)	(0.028)	(0.085)	(0.095)	(0.026)	(0.054)	(0.017)

#### **TABLE II. PERFORMANCE RATINGS:**

17.5212 III 1 21.11 0 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11 11.11											
	CU	RRENT	RATING	S**		TIME TO	RESISTANCE		TRIPPED-STATE		
						TRIP**	VALUES		POWER		
									DISSIPATION**		
AMPS		AM	PS	AMPS		SECONDS AT	OHMS		WATTS AT		
AT 0°C		AT 20°C		AT 60°C		20°C, 8.0A	AT 20°C		20°C		
HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MAX	MIN	MAX*	MAX		
1.36	3.29	1.20	2.30	0.83	1.60	2.0	0.150	0.340	2.2		

<sup>\*</sup> Maximum resistance is measured 1 hour after reflow.

Reference Documents: PS300, PS400

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

### **Materials Information**

**ROHS Compliant** 

ELV Compliant

Pb-Free

Halogen Free\*

Directive 2002/95/EC Compliant Directive 2000/53/EC Compliant



HF

<sup>\*\*</sup> Values specified were determined using PCB's with 0.100"X2.0 ounce copper traces.

<sup>\*</sup> Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.



# PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: AHS120

DOCUMENT: SCD28207 REV LETTER: B

REV DATE: JULY 26, 2016 PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.