

Data sheet | Item number: 745-632

Jumper; 2-way; silver-colored

www.wago.com/745-632



Data

Electrical data

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

**Ratings per IEC/EN**

Rated current	76 A
---------------	------

Physical data

Pin spacing	15 mm / 0.591 inches
Jumper assignment	1-2

Mechanical Data

Suitable	for 745 Series (16 mm ²) and 2716 Series
----------	--

Material Data

Note (material data)	Information on material specifications can be found here
----------------------	--

Color	silver-colored
Contact material	Copper alloy
Contact plating	Tin
Weight	3.9 g

Commercial data

Product Group	4 (Printed Circuit Connectors)
eCl@ss 10.0	27-14-11-40
eCl@ss 9.0	27-44-04-92
ETIM 8.0	EC000489
ETIM 7.0	EC000489
PU (SPU)	200 (50) pcs
Packaging type	box
Country of origin	CH
GTIN	4045454149758
Customs tariff number	85366990990

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads**Documentation**

Subject to changes. Please also observe the further product documentation!

Additional Information

2019 年4月3日

pdf
2.0 MB

[Download](#)

CAD/CAE-Data

CAD data

2D/3D Models 745-632

[URL](#)

[Download](#)

CAE data

ZUKEN Portal 745-632

[URL](#)

[Download](#)

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 745-632

[URL](#)

[Download](#)

Jumper; 2-way; silver-colored

Installation Notes



Inserting a comb-style jumper bar.



To insert a comb-style jumper bar, push it down using a screwdriver until it hits the backstop – 745 Series.

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



To remove the jumper bar, lift it up using a screwdriver – 745 Series.

Subject to changes. Please also observe the further product documentation!