

**Data sheet | Item number: 211-824**

Nozzles; Length: 23 mm; For the use of 211-821; halogen-free; Cable outer diameter: 5.0 ... 11.0 mm; transparent

[www.wago.com/211-824](http://www.wago.com/211-824)



**Data**

**Technical data**

Suitable	for wire diameter 5 ... 11 mm
Delivery form	Component
Properties	for one 211-821 marker
Printing device	Smart Printer (Thermal Transfer Printer)

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Physical data

Length	23 mm
Sheathed cable diameter	5 ... 11 mm

## Mechanical Data

Mounting type	Sliding on conductor
---------------	----------------------

## Material Data

Color	transparent
Material	Polyurethane
Adhesive information	without adhesive
Halogen-free	Yes
Weight	1.2 g

## Environmental requirements

Ambient temperature (storage)	+5 ... +40 °C
Ambient temperature (operation)	-40 ... +80 °C
Relative humidity	40 ... 80 %

## Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	200 pcs
Packaging type	box
Country of origin	IT
GTIN	4050821675020
Customs tariff number	39269097900

## Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Subject to changes. Please also observe the further product documentation!



## Required accessories

### Marking accessories

Marker

Item no.: 211-821

Marker; for Smart Printer; for use in nozzles; Length: 23 mm; white

[www.wago.com/211-821](http://www.wago.com/211-821)

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 211-824

URL

Download

Nozzles; Length: 23 mm; For the use of 211-821; halogen-free; Cable outer diameter: 5.0 ...11.0 mm; transparent

## Installation Notes

### Application



Slide the marker into the marking sleeve receptacle. Replacing the marker is also possible after the conductor has been terminated.

### Application

Subject to changes. Please also observe the further product documentation!



Compress the sleeve and slide it onto the conductor to be marked.

Subject to changes. Please also observe the further product documentation!