

designed and manufactured in Germany

Data Sheet IPM-165

Version 8.5 - 02.04.2014

PRODUCT FAMILY

Low Cost K-Band Transceiver


APPLICATIONS

- Security applications
- Door openers
- Industrial applications

1.00	
	Movement
	Velocity
	Direction
	Presence
	Distance
	Angle

FEATURES:

- » radar-based motion detector working in the 24GHz ISM Band
- » available in different frequency ranges for worldwide use
- » advanced LCO-oscillator with low current consumption
- » split transmit and receive path for maximum gain
- » very compact outline dimensions



DESCRIPTION

The IPM-165 is a 24GHz Doppler module with an asymmetrical wide beam for detection of moving objects.

Low power consumption components are quickly enabled supporting duty cycles for battery or solar panel operation.

Certified and approved according to

- ETSI EN 300 440
- FCC part 15.245 (UXS-IPM165)
- IC RSS210 Issue 7 (6902A-IPM165)

ADDITIONAL INFORMATION

InnoSenT Standard Product. Changes will not be notified as long as there is no influence on form, fit and within this datasheet specified function of the product.

CERTIFICATES

InnoSenT GmbH has established and applies a quality system for: development, production and sales of radar sensors for industrial and automotive sensors.



RoHS-INF0

This product is compliant to the restriction of hazardous substances (RoHS - European Union directive 2011/65/EU).

CONFIDENTIAL AND PROPRIETARY



ELECTRICAL CHARACTERISTICS

PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNITS

Oscillator

transmit frequency ¹	@ 25°C	f _{standard}	24.050		24.250	GHz
	US-frequency band @ 25°C	f _F	24.075		24.175	GHz
	UK-frequency band @ 25°C	f _{uk}	24.150		24.250	GHz
output power		P _{out}		16	20	dBm
temperature drift		∆f		-1		MHz/°C

Receiver

IF-output	voltage offset	-300	300	mV
Signal level ²	category A	563	855	mV _{P-P}
	category B	856	1177	mV _{P-P}
	category C	1178	1819	mV _{P-P}
Noise level ²	R		116	mV

Power supply

supply voltage	V _{cc}	4.75	5.00	5.25	V
supply current	I _{cc}	18	30	40	mA

Environment

operating temperature	Τ _{ορ}	-20	+60	°C
storage temperature	T _{storage}	-20	+60	°C

Mechanical Outlines

outline dimensions	length width height	25 25 7 (12.7)	mm
--------------------	---------------------------	----------------------	----


¹ Details to the frequency bands you can find in Annex A

² Relative output signal level and noise is measured at room temperature in a dedicated InnoSenT test setup

CONFIDENTIAL AND PROPRIETARY




ANTENNA ORIENTATION:



ROTATIONAL PIVOT antenna centroid

TX / RX-ANTENNA PATTERN:



PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNITS	
TX-antenna pattern / RX-antenna pattern							
Tx antenna pattern (3dB width)	horizontal	azimuth		80		0	
	vertical	elevation		35		o	
side-lobe suppression	horizontal	azimuth		12		dB	
	vertical	elevation		13		dB	
squinting angle				0		o	
Antenna gain				9.5		dBi	

CONFIDENTIAL AND PROPRIETARY




INTERFACE


The sensor provides a 2.54mm grid, single row pin header (square pin□0.635mm)

PIN #	DESCRIPTION	IN / OUT	COMMENT
1	V _{cc}	input	supply voltage (4.75 - 5.25V)
2	IF1	output	signal I(nphase)
3	GND	input	analog ground

MECHANICAL OUTLINES



Labeling



165

Version 8.5

CONFIDENTIAL AND PROPRIETARY




Annex A

The IPM-165 is available in different frequency ranges for worldwide use. Depending on the country in which the product is intended to be used, different frequency ranges can be ordered at InnoSenT. The information that will be given below is only a rough overview; for details please contact the local approval agencies. An overview over the frequency bands in Europe can also be found in the REC 70-03 (Annex 6) which is

Frequency Bands in Europe

available under www.ero.dk

Generally the IPM-165 standard version can be used for all countries in Europe except for the UK. For the UK market you have to order the IPM-165_UK modules to be conform with the regulations of the UK-Approval-Agency.



Frequency Bands in US

For the US-market the IPM-165_F version has to be used!



InnoSenT has a limited modular approval for the IPM-165_F with the following grant: UXS1

FCC approval

This device complies with Part 15 of the FCC Rules and with RSS-210 of Industry Canada. Operation is subject to the following two conditions:

(1) this device may not cause harmful interference, and

(2) this device must accept any interference received, including interference that may cause undesired operation.

Warning: Changes or modifications made to this equipment not expressly approved by InnoSenT GmbH may void the FCC authorization to operate this equipment.

Manufacturers of mobile or fixed devices incorporating IPM-165 modules are authorized to use the FCC Grants and IC Certificates of the IPM-165 modules for their own final products according to the conditions referenced in these documents. In this case, the FCC label of the module shall be visible from the outside, or the host device shall bear a second label stating "Contains FCC ID: UXS-IPM165F" and "Contains IC: 6902A-IPM165".

CONFIDENTIAL AND PROPRIETARY



ESD-INFORMATION



This InnoSenT sensor is sensitive to damage from ESD. Normal precautions as usually applied to CMOS devices are sufficient when handling the device. Touching the signal output pins has to be avoided at any time before soldering or plugging the device into a motherboard.

APPROVAL

This Data Sheet contains the technical specifications of the described product. All previous versions of this Data Sheet are no longer valid.

The sensor uses Hydrocarbon based material which may change its dielectric properties when used in an oxidative environment. This may vary based on temperature. Therefore InnoSenT recommends evaluating this influence within the specific environment.

VERSION	DATE	COMMENT
8.2	06.03.2013	new layout
8.3	24.10.2013	FCC ID updated
8.4	06.12.2013	Max. output power added + Min. supply current added + modified format
8.5	02.04.2014	Antenna orientation + system pattern

InnoSenT GmbH

Am Rödertor 30 97499 Donnersdorf GERMANY Tel.: +49 (0) 9528 - 9518 - 0 E-Mail: info@innosent.de URL: www.innosent.de