

Compression Washers - ROHS Compliant**Use for Snap-In Panel Style Units****Mounting -**

Panel hole $1.063 \pm .005$ diameter should be punched from the back side so that locking fingers enter on a slightly rounded edge of the hole. Assemble proper compression washer and press into panel hole until locking fingers snap over the hole edge. Installation pressure should be applied at the circumference of the device.

Catalog Number	Thickness (A)	Panel Thickness (B)
PW1	.063	11-12GA (.125-.109)
PW2	.125	13-17GA (.093-.056)
PW3	.187	18-22GA (.050-.031)

Material: Black ester foam

Compression: 5:1

