

**Data sheet | Item number: 211-923**

Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 2.0 ... 4.0 mm; transparent

[www.wago.com/211-923](http://www.wago.com/211-923)



**Data**

**Technical data**

Suitable	for wire diameter 2 ... 4 mm
Delivery form	Component
Properties	for one 211-821 marker
Printing device	Smart Printer (Thermal Transfer Printer)

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Physical data

Length	23 mm
Sheathed cable diameter	2 ... 4 mm

## Mechanical Data

Mounting type	Sliding on conductor
---------------	----------------------

## Material Data

Color	transparent
Material	Polyvinyl chloride
Adhesive information	without adhesive
Halogen-free	No
Weight	0.3 g

## Environmental requirements

Ambient temperature (storage)	+5 ... +40 °C
Ambient temperature (operation)	-15 ... +70 °C
Relative humidity	40 ... 80 %

## Commercial data

eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	500 pcs
Packaging type	bag
Country of origin	IT
GTIN	4055143381178
Customs tariff number	39269097900

## Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

## Required accessories

### Marking accessories

Subject to changes. Please also observe the further product documentation!

Marker

Item no.: 211-821

Marker; for Smart Printer; for use in nozzles; Length: 23 mm; white

[www.wago.com/211-821](http://www.wago.com/211-821)

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 211-923

URL

Download

Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 2.0 ... 4.0 mm; transparent

## Installation Notes

### Application



Slide the marker into the marking sleeve receptacle. Replacing the marker is also possible after the conductor has been terminated.

### Application

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



Compress the sleeve and slide it onto the conductor to be marked.

Subject to changes. Please also observe the further product documentation!