




## MDCDK41-11-11-A

Ruland MDCDK41-11-11-A, 11mm x 11mm Double Disc Coupling, Aluminum, Clamp Style With Keyway, 41.3mm OD, 55.0mm Length





## Description

Ruland MDCDK41-11-11-A is a clamp double disc coupling with 11mm x 11mm bores, 41.3mm OD, 55.0mm length, and 4mm x 4mm keyways. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The double disc design is comprised of two anodized aluminum hubs, two sets of thin stainless steel disc springs, and a center spacer allowing each disc to bend individually and accommodate all types of misalignment. MDCDK41-11-11-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MDCDK41-11-11-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. MDCDK41-11-11-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications	Product	Specifi	cations
------------------------	---------	---------	---------

Product Specifications			
Bore (B1)	11 mm	Small Bore (B2)	11 mm
Keyway (K1)	4 mm	Keyway (K2)	4 mm
B1 Max Shaft Penetration	26.1 mm	B2 Max Shaft Penetration	26.1 mm
Outer Diameter (OD)	41.3 mm	Bore Tolerance	+0.03 mm / -0.00 mm
Length (L)	55.0 mm	Hub Width (LH)	18.05 mm
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Forged Clamp Screw	M4
Screw Material	Alloy Steel	Hex Wrench Size	3.0 mm
Screw Finish	Black Oxide	Seating Torque	4.6 Nm
Number of Screws	2 ea	Dynamic Torque Reversing	5.08 Nm
Angular Misalignment	2.0°	Dynamic Torque Non-Reversing	10.15 Nm
Parallel Misalignment	0.25 mm	Static Torque	20.3 Nm
Axial Motion	0.51 mm	Torsional Stiffness	42.4 Nm/Deg
Moment of Inertia	3.8540 x 10 <sup>-5</sup> kg-m <sup>2</sup>	Maximum Speed	10,000 RPM
Zero-Backlash?	Yes	Balanced Design	Yes
Torque Wrench	TW:BT-1R-1/4-41.0	Recommended Hex Key	Metric Hex Keys
Full Bearing Support Required?	Yes	Material Specification	Hubs and Center Spacer: 2024-T351 Aluminum Bar Disc Springs: Type 302 Stainless Steel
Temperature	-40°F to 200°F (-40°C to 93°C)	Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (Ibs)	0.326100	UPC	634529175316
Tariff Code	8483.60.8000	UNSPC	31163008
Note 1	Stainless steel hubs are available upon request.		
Note 2	Torque ratings are at maximum mis	salignment.	
Note 3	Performance ratings are for guidan	ce only. The user must determine su	itability for a particular application.
Note 4	normal/typical conditions the hubs cases, especially when the smalles	e based on the physical limitations/fa are capable of holding up to the rated st standard bores are used or where s rque of the disc springs. Keyways are	d torque of the disc springs. In some shafts are undersized, slippage on th

	torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.	
Prop 65	<b>WARNING</b> This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to <u>www.P65Warnings.ca.gov</u> .	
Installation Instructions		
	<ol> <li>Align the bores of the MDCDK41-11-11-A double disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (<i>Angular</i> <i>Misialignment:</i> 2.0°, <i>Parallel Misalignment:</i> 0.25 mm, <i>Axial Motion:</i> 0.51 mm)</li> <li>Fully tighten the M4 screw on the first hub to the recommended seating torque of 4.6 Nm using a 3.0 mm hex torque wrench.</li> <li>Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.</li> <li>Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.</li> <li>The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 26.1 mm.</li> </ol>	