



MADE
IN THE **USA**

Product Description:

- Bundle Includes:
 - LD-070 Protection System
 - Holds disposable or reusable gowns, aprons, or coveralls/jumpsuits, three boxes of gloves, one box of earloop masks, and one box of shield masks
 - Quartz Beige ABS Plastic
 - MB-600 Hanger - Door - Standard
 - Hooks over top of door no thicker than 2.44"
 - Quartz Beige Powder-Coated Steel

Primary Area for Product Usage:

- Anywhere protective equipment products are needed

Dispenses:

- Top: Box(es) no larger than 5.00"W x 10.00"H x 4.49"D (12.7 cm x 25.4 cm x 11.4 cm)
- Bottom left: Gowns, aprons, or coveralls/jumpsuits no larger than 11.38"W x 15.30"H x 4.53"D (28.9 cm x 37.4 cm x 11.5 cm)
- Middle right: Box(es) no larger than 8.39"W x 5.24"H x 4.49"D (21.3 cm x 13.3 cm x 11.4 cm)
- Bottom right: Box(es) no larger than 8.39"W x 9.80"H x 4.49"D (21.3 cm x 24.9 cm x 11.4 cm)

Product Specifications (overall assembled dimensions):

- 20.05"W x 36.16"H x 7.30"D (50.9 cm x 91.8 cm x 18.5 cm)
- 5.4 lbs (2.4 kg) - approximated

Package Specifications:


- Package Quantity: 1 per case
- 29"W x 6"H x 23"D (73.7 cm x 15.2 cm x 58.4 cm)
- 8.0 lbs (3.6 kg) - approximated



Consumables not included

Mounting Specifications:

- Left: Protection System, Right: Door Hanger






Installation


Always mount dispensers securely *prior* to loading with product.

- Proper Hanging Procedure:
 - 1) Attach hanger securely - back of hanger must lay flush against surface.



1

- 1) Hang dispenser on hanger.
- 2) Load product in dispenser.
- 3) To remove, reverse order of steps.



2

Parts included:

- Protection System
- Door Hanger

Tools Required:

- No tools required to assemble dispenser

Care and Construction

ABS Plastic

Material Characteristics

Designed for Long-Term, Heavy-Duty Applications

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness.

ABS is chemical, stress-crack resistant, dimensionally stable, and will hold up to long-term use. It possesses high strength and performance characteristics at a reasonable cost.

Care and Cleaning

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.

Powder-Coated Steel

Material Characteristics

Designed for Long-Term Use

Our steel dispensers and stands are coated with polyester powders which makes them highly resistant to corrosion.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting because it is impact resistant and is not effected by extremes in temperature.

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service.

Care and Cleaning

For best results, clean by washing the surface with a diluted solution of a mild, non-abrasive detergent in cold or warm water and a non-abrasive cloth. Standard hospital cleaning supplies can be used.

Dry with a soft cloth. Do not use any solvent-based materials, abrasives (e.g. Scotch-brite, steel wool), or apply excessive force during cleaning.