


OMRON

NEW

Digital Bar Ionizer
ZJ-BAS



Effective and Efficient Ionization



realizing



Effective and Efficient Ionization


The highest level of ionization in its class.

Advanced Features in 3 Aspects



[Wide Area]


Ionizes areas wider than the ionizer itself.



[Short Distance]

Achieves the highest level of short-distance ionization in its class.

■ Installation distance: 50 mm




Measurement conditions:
ZJ-BAS058
Frequency setting: 20 Hz
Air pressure: 0.3 Mpa
Charge plate monitor: 150 mm X 150 mm, 20 pF
Ionization time: ±1,000 V to ±100 V

[Long Distance]

Steady ionizing performance, even over long distances.

■ Installation distance: 1,500 mm




Measurement conditions:
ZJ-BAS058
Frequency setting: 20 Hz
Air pressure: 0.3 Mpa
Charge plate monitor: 150 mm X 150 mm, 20 pF
Ionization time: ±1,000 V to ±100 V

Three Technologies Supporting Effective and Efficient Ionization

Industry First


Technology 1 Ion Sensing and Variable-AC System

An ion sensor installed on the bottom of the ionizer detects the charge and ion balance. The applied voltage is flexibly controlled according to the ion balance conditions to raise ionization efficiency.



Technology 2 Micro Power Spraying (MPS) Structure

High-speed airflow is achieved by minimizing the air nozzle diameter. An optimal cone shape is also employed for the inside of the nozzle to further improve ion dispersion. By using a special ring guard shape to pull passive air into the active air stream, the total airflow is dramatically increased.




Technology 3 Optimized Discharge Electrode Pitch

Setting the discharge electrodes at a pitch that is 80 mm longer than in our previous models achieves an optimal layout that unifies ionizing performance and reduces ion recombination. This model ionizes over long distances with or without the use of an Air Purge Ionizer.

■ ZJ-BAS


A small amount of ion recombination.




■ Previous Models

A large amount of ion recombination.

The larger pitch causes uneven ion discharge.



Linking
up to 7 Units*



A New Proposal for Effective and Efficient Ionization

Uniform Ionization

Linked Ionizers cover a wide area without causing uneven ionization.


Long Ionizers are required to meet the needs of increasingly large liquid crystal glass panels. Ionizers as long as two meters are not only difficult to transport and install, but also pose difficulties in achieving uniform ionization. The highly thorough ZJ-BAS Ionizer solves this problem by connecting Ionizers together.

* For information on requirements for linking ionizers, contact your OMRON sales representative.

Two Forms of Uniform Ionization Achieved by Linking Function


Uniform Airflow

The air supply ports on previous models were only on both ends, so the airflow was weak in the center of long ionizers. By connecting ZJ-BAS ionizers together, air is supplied from the center part as well, thus achieving a uniform airflow and eliminating uneven ion discharge at medium and long distances.



Uniform Ion Balance


For example, when both sides of a workpiece are charged, a long ionizer will adjust the amount of ions according to the entire ionizer length, so an area that is not charged may take on a reverse charge. By using linked ZJ-BAS ionizers, each ionizer senses the charge condition. Because only the ionizers on both ends then control their ion amounts in response to the charges, reverse charging does not occur.



Technologies that Support Uniform Ionization

Technology 1 Supplying air with no pressure loss

By arranging discharge electrodes on both ends, the ionizer can handle an area wider than the length of the ionizer itself. This eliminates dead zones even when linking ionizers, and achieves uniform ionization.



Technology 2 Ion Sensing and variable-AC system prevents ion recombination


Because the ZJ-BAS ionizer uses a method in which the linked ionizers operate using the same power supply, the positive and negative ion generation timing between the ionizers is synchronized. Also, the sensing and variable-AC system control the amount of ions while synchronizing the ionizers. This reduces ion recombination between the linked ionizers, and achieves uniform ionization.

Ion Sensing and Variable-AC System

The amount of ions is adjusted even when a charge is detected, so synchronization with matching polarity is maintained.

AC System

If the synchronization of the timing is lost, the polarity is reversed.



Improving Ease of Use

The Digital Ion Display Supports Safe, Reliable Settings.



From either the Remote Control or the Ionizer...

The Digital Ion Display guides you when making settings. Settings that are important for ionization performance, such as the frequency and ion balance, can be made and displayed safely and reliably from the ionizer itself, or by using the Remote Control.



Settings can be made from the Ionizer itself.



ZJ-BAS-R01/R02 (Sold separately)

A Variety of Displays

Ion Balance Display

The charged state is displayed using colors.

Negative ions Positive ions



When there are many negative ions



When there are many positive ions



Set Value Display

The current set value is shown on the right side of the display. The set value can be numerically confirmed, so the setting can be quantified. This allows identical settings to be made reliably and in a short time even across multiple ionizers.

Frequency setting



Ion balance adjustment



Cleaning sensitivity



Cleaning Display

Notifies when cleaning is required.



Setting Lock

Disables all operations.



Operation Stop Mode Makes Maintenance Easy

The Operation Stop Mode allows for safe cleaning and replacement work. The digital display and LED lamps tell you that the ionizer is in Operation Stop Mode so you won't forget to return to Operation Mode when you are finished doing maintenance. Both regular operations and maintenance can be done safely and reliably.

Operation Stop Mode



The LED lamp will flash to indicate that the ionizer is in Operation Stop Mode.


Operations from external equipment, such as stopping ionization and performing status management, can be done easily by connecting the ionizer to a PLC using an I/O cable.



PLC

M.P.S. Construction Prolongs the Required Maintenance Period by 5 Times Compared to Our Previous Model Greatly Reduces Maintenance Requirements


The M.P.S. nozzle emits clean air from around the discharge electrode, thus decreasing the amount of foreign matter adhesion, and dramatically extending the time before cleaning is required.



Energy-saving is a Basic Concept for OMRON Ionizers

Generally, bar-type ionizers use compressed air. Therefore, a large amount of compressed air is needed, especially for long-distance or high-speed ionization. This increases the load rate of the compressor, and consumes large amounts of electricity. The ZJ-BAS uses an optimized discharge electrode pitch and M.P.S. nozzle to improve ionization performance while using an energy-saving structure (low-current consumption) that is environmentally friendly.

The M.P.S. nozzle allows for efficient airflow while reducing current consumption.




Ring guard

80-mm Discharge Electrode Pitch Dramatically Reduces Replacement Costs

The 80 mm discharge electrode pitch and variable-AC system reduce the number of discharge electrodes required by 60%. In addition to reducing the cleaning time, the periodic replacement of the electrodes has also been reduced, thereby dramatically reducing the running cost of the ionizer.


| Effective length (mm) | Number of Discharge Modules |
|-----------------------|-----------------------------|
| 500 | 5 |
| 580 | 6 |
| 740 | 8 |
| 900 | 10 |
| 1300 | 15 |
| 1540 | 18 |




Low Running Cost.

Engineering Data

Relationship of Air Pressure and Installation Distance to Ionization Time




Bar Length vs. Air Pressure and Airflow




Ionization Time for Each Ionization Area

With installation distance of 50 mm (reference value)



With installation distance of 1,500 mm (reference value)



Product Configuration

Ionizer ZJ-BAS



I/O Cable ZJ-BAS-FC

Used for connecting external devices.




Power supply cable

Select from the two available types.


Cable with Connector on One End

ZJ-BAS-MC□□A
Used when using a DC power supply.



Cable with Connectors on Both Ends

ZJ-BAS-MC□□B
Used when using an AC adapter.



AC Adapter ZJ-BAS-PS01




Special Remote Control


Remote Control
ZJ-BAS-R01



Remote Control Receiver
ZJ-BAS-R02



When Linking Ionizers




ZJ-BAS-MC□□RB Power Supply Cable (for linking ionizers)

The length of the cables that can be linked depends on the number of ionizers to be linked together. Contact your OMRON sales representative for details.






Ordering Information


Ionizer

| Appearance | Total length | Effective length | Model |
|---|--------------|------------------|-----------|
|  | 370 mm | 500 mm | ZJ-BAS050 |
| | 450 mm | 580 mm | ZJ-BAS058 |
| | 610 mm | 740 mm | ZJ-BAS074 |
| | 770 mm | 900 mm | ZJ-BAS090 |
| | 1170 mm | 1300 mm | ZJ-BAS130 |
| | 1410 mm | 1540 mm | ZJ-BAS154 |


Power Supply Cable

| Appearance | Type | Cable length | Model |
|---|---|--------------|---------------|
|  | Cable with Connector on One End (one ferrite core provided, 30-dia X 39 mm) | 2 m | ZJ-BAS-MC02A |
| | | 5 m | ZJ-BAS-MC05A |
| | | 10 m | ZJ-BAS-MC10A |
| | | 15 m | ZJ-BAS-MC15A |
| | | 20 m | ZJ-BAS-MC20A |
|  | Cable with Connectors on Both Ends (one ferrite core provided, 30-dia X 39 mm) | 2 m | ZJ-BAS-MC02B |
| | | 5 m | ZJ-BAS-MC05B |
| | | 10 m | ZJ-BAS-MC10B |
| | | 15 m | ZJ-BAS-MC15B |
| | | 20 m | ZJ-BAS-MC20B |
|  | Used for connecting Ionizers | 710 mm | ZJ-BAS-MC07RB |
| | | 790 mm | ZJ-BAS-MC08RB |
| | | 950mm | ZJ-BAS-MC09RB |
| | | 1110 mm | ZJ-BAS-MC11RB |
| | | 1510 mm | ZJ-BAS-MC15RB |
| | | 1750 mm | ZJ-BAS-MC17RB |



I/O Cable

| Appearance | Cable length | Model |
|---|--------------|--------------|
|  | 2 m | ZJ-BAS-FC02A |
| | 5 m | ZJ-BAS-FC05A |
| | 10 m | ZJ-BAS-FC10A |
| | 15 m | ZJ-BAS-FC15A |
| | 20 m | ZJ-BAS-FC20A |


AC Adapter

| Appearance | Specifications | Model |
|---|---|-------------|
|  | Input: 100 to 240 VAC Output: 24 VDCx2 | ZJ-BAS-PS01 |


Special Remote Control

| Appearance | Type | Model |
|---|---|------------|
|  | Remote Control | ZJ-BAS-R01 |
|  | Remote Control Receiver (Receiver, USB cable, bracket) | ZJ-BAS-R02 |


Linking Bracket Set

| Appearance | Contents | Model |
|---|--|-------------|
|  | Linking Bracket (1) 6-dia. Elbow Air Joint (x2) | ZJ9-BAS-L01 |

Discharge Electrode Module

| Appearance | Quantity | Model |
|---|-----------|---------------|
|  | Set of 5 | ZJ9-BAS-NT105 |
| | Set of 10 | ZJ9-BAS-NT110 |

Cleaning Tool

| Appearance | Quantity | Model |
|---|---------------|-------------|
|  | Set of 20 jig | ZJ9-BA-CT01 |

Ratings and Characteristics

Ionizer

| Item | Model | ZJ-BAS050 | ZJ-BAS058 | ZJ-BAS074 | ZJ-BAS090 | ZJ-BAS130 | ZJ-BAS154 |
|---------------------------------------|--------|---|-----------------|----------------|-----------------|--|----------------|
| Ionizer length (mm) | | 370 | 450 | 610 | 770 | 1170 | 1410 |
| Effective ionization length (mm) (*1) | | 500 | 580 | 740 | 900 | 1300 | 1540 |
| Power supply voltage | | 24 VDC ±10%, ripple (p-p) 10% max. | | | | | |
| Current consumption | | 520 Ma max. (discharge frequency 0.08 to 0.5 Hz: 400 mA (typical), 1 to 10 Hz: 350 mA (typical), 20 to 40 Hz: 300 mA (typical)) | | | | | |
| Discharge method | | Sensing and a Variable-AC System | | | | | |
| Discharge voltage | | 6.5 k VP-P | | | | | |
| Discharge electrode | | Tungsten electrode | | | | | |
| Recommended installation distance | | 50 to 2,000 mm | | | | | |
| Ion balance (*2) | | ±30 V max. | | | | | |
| Power supply connector | | Modular type, 8-pin connector (at both ends of Unit) | | | | | |
| Air inlet | | 6-dia one-touch coupling (at both ends of Unit) | | | | | |
| Maximum air pressure | | 0.3 MPa max. | | | | | |
| External I/O | Input | Discharge stop input (Turns ON at 12 to 24 VDC), input impedance: 8.2 kΩ | | | | | |
| | Output | Discharge stop output, cleaning output, alarm output, high-pressure error output: Signal output from photo MOS relay (100 mA max at 24 VDC) | | | | | |
| Display | | Seven-segment LED display | | | | | |
| ID number | | 001 to 050 | | | | | |
| Ion balance adjustment function | | Yes | | | | | |
| Maximum number of linkable units | | 7 Units | | | | | |
| Material | | Ionizer: ABS-resin, facing electrodes: Stainless steel | | | | | |
| Ambient temperature range | | Operating: 10 to 40°C, Storage: 0 to 40°C (with no icing or condensation) | | | | | |
| Ambient humidity range | | Operating: 35% to 65%, Storage: 35% to 85% (with no condensation) | | | | | |
| Weight (Ionizer only) | | Approx. 0.58 kg | Approx. 0.64 kg | Approx. 0.8 kg | Approx. 0.94 kg | Approx. 1.28 kg | Approx. 1.5 kg |
| Accessories | | Two mounting brackets, two M4 screws, instruction manual | | | | Two mounting brackets, two M4 screws, 1 medium bracket, instruction manual | |

*1 Measurement conditions Installation distance: 50 mm

Airflow: 1 L /min per hole

Frequency: 10 Hz

Charge plate monitor: 150 × 150 mm, 20 pF

Ionization time: (1,000 V→100V/–1,000V→–100V): 1 s max.)

*2 Measurement conditions Installation distance: 300 mm

Airflow: 1 L /min per hole

Frequency: 10 Hz

Charge plate monitor: 150 × 150 mm, 20 pF

AC Adaptor

| Item | Model | ZJ-BAS-PS01 |
|--------------------------|-------|--|
| Input voltage | | 100 to 240 VAC |
| Input current | | 1.2A max. |
| Output voltage | | 24 VDC |
| Output current | | 3.75A max. |
| Number of output ports | | 2 ports |
| Product configuration | | Adaptor box, AC adaptor AC power cable |
| Weight (without package) | | Adapter box: Approx. 30 g AC Adaptor: Approx. 430 g AC power supply cable: Approx. 260 g |


Special Remote Control

| Item | Model | ZJ-BAS-R01 | ZJ-BAS-R02 |
|----------------------------------|-------|-------------------------|---|
| Product configuration | | Remote Control only | Receiver Cable (150 mm) Brackets (not including Remote Control) |
| Communications method | | Infrared communications | |
| Number of detectable Units | | 50 Units | – |
| Power supply | | Three AAA batteries | Supplied from the ZJ-BAS Ionizer |
| Weight (not including packaging) | | Approx. 115 g | Receiver: Approx. 5 g Cable: Approx. 6 g Bracket: Approx. 5 g |
| Accessories | | Instruction manual | |

Dimensions

(Units: mm)


Ionizer



The dimensions and number of Discharge Electrode Modules for each model are shown in the following table.


| Model | A (mm) | B (mm) | C (mm) | Discharge Electrode Module |
|-----------|--------|--------|--------|----------------------------|
| ZJ-BAS050 | 370 | 394 | 416 | 5 |
| ZJ-BAS058 | 450 | 474 | 496 | 6 |
| ZJ-BAS074 | 610 | 634 | 656 | 8 |
| ZJ-BAS090 | 770 | 794 | 816 | 10 |
| ZJ-BAS130 | 1170 | 1194 | 1216 | 15 |
| ZJ-BAS154 | 1410 | 1434 | 1456 | 18 |

Mounting bracket



Auxiliary mounting bracket

Provided with the ZJ-BAS130/BAS154




Dimensions


(Units: mm)

Power Supply Cable

ZJ-BAS-MC□□A




ZJ-BAS-MC□□B/MC□□RB



I/O Cable


ZJ-BAS-FC□□A



AC Adapter


(Adapter box)

ZJ-BAS-PS01



Remote Control


ZJ-BAS-R01



Receiver for the Remote Control


(Bracket)

ZJ-BAS-R02




Linking Bracket

ZJ9-BAS-L01



Material: Stainless steel (SUS304)



This document provides information mainly for selecting suitable models. Please read the Instruction Sheet carefully for information that the user must understand and accept before purchase, including information on warranty, limitations of liability, and precautions.

OMRON Corporation
Industrial Automation Company
Sensing Devices Division H.Q.
Application Sensors Division

Shiokoji Horikawa, Shimogyo-ku,
Kyoto, 600-8530 Japan
Tel: (81) 75-344-7068/Fax: (81) 75-344-7107

Regional Headquarters

OMRON EUROPE B.V.

Sensor Business Unit
Carl-Benz-Str. 4, D-71154 Nufringen,
Germany
Tel: (49) 7032-811-0/Fax: (49) 7032-811-199

OMRON ELECTRONICS LLC

One Commerce Drive Schaumburg,
IL 60173-5302 U.S.A.
Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),
Alexandra Technopark, Singapore 119967
Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2008 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.