

Flux Remover (Fast Evaporating) in 15ml (0.5oz) Squeeze Bottle w/tip

Product Highlights

A Flux Remover that is Non-Flammable and Fast Evaporating

Can be used with Leaded and Lead-Free applications

RoHS 3 and REACH compliant

Specifications

Packaging:

15ml Squeeze Bottle

Shelf Life:

Refrigerated >24 months, Unrefrigerated >24 months



Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). The flux remover can be allowed to freeze. Freezing will not degrade this product. Allow 4 hours for flux remover to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

Conforms to the following Industry Standards:

RoHS 3 Directive (EU) 2015/863:

Yes

Flux Remover Selection Guide

| Description | Packaging | Orderable Part Number |
|--|-----------------------|-----------------------|
| Degreaser / Contact Cleaner (Non-Flammable) | Pen, 10ml | CQNRM |
| | Squeeze Bottle, 0.5oz | CQNRM-0.5 |
| | Squeeze Bottle, 1.0oz | CQNRM-1.0 |
| Flux Remover (Non-Flammable) | Pen, 10ml | CQNTRM |
| | Squeeze Bottle, 0.5oz | CQNTRM-0.5 |
| | Squeeze Bottle, 1.0oz | CQNTRM-1.0 |
| Flux Remover (Fast Evaporating, Non-Flammable) | Pen, 10ml | CQNIRM |
| | Squeeze Bottle, 0.5oz | CQNIRM-0.5 |
| | Squeeze Bottle, 1.0oz | CQNIRM-1.0 |
| Flux Remover (Foam-Free, Flammable) | Pen, 10ml | CQIRM |
| | Squeeze Bottle, 0.5oz | CQIRM-0.5 |
| | Squeeze Bottle, 1.0oz | CQIRM-1.0 |
| Flux Remover (Foaming, Flammable) | Pen, 10ml | CQ6RM |
| | Squeeze Bottle, 0.5oz | CQ6RM-0.5 |
| | Squeeze Bottle, 1.0oz | CQ6RM-1.0 |