LE B P1MQ

OSRAM OSTAR® Projection Power

OSRAM OSTAR Projection Power is a high luminance LED for projection applications.



Applications

- Projection Home LED & Laser

- Projection Professional LED & Laser


Features:

- Package: OSTAR High Power Projection
- Chip technology: UX:3
- Typ. Radiation: 120° (Lambertian emitter)
- Color: λ_{dom} = 456 nm (• blue)
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)

Ordering Information

Туре	Total radiant flux ¹⁾ I _F = 6000 mA Φ _e	Ordering Code
LE B P1MQ-FPFT-23	11200 16400 mW	Q65112A7815





Maximum Ratings

Cymbol	Symbol	
T _{stg}	min.	-40 °C
U U	max.	85 °C
T _j	max.	150 °C
I _F	min.	200 mA
	max.	10000 mA
F pulse		12000 mA
i puoo		
I _{ES}	max.	14000 mA
V _{ESD}		2 kV
LOD		
I _R	max.	200 mA
$ \Delta V_{a-b} , \Delta V_{c-b} $	max.	40 V
	I I _F I _{F pulse} I _{FS} V _{ESD} I _R	max.Tjmax.IFmin. max.IFmax.IFmax.IFmax.IFmax.

OS-IN-2021-008-A



Characteristics

 T_{Board} = 25 °C; I_F = 6000 mA; f = 1000 Hz; D = 0.25

Parameter	Symbol		Values
Peak Wavelength	λ_{peak}	typ.	450 nm
Dominant Wavelength 3)	λ_{dom}	min.	452 nm
	dom	typ.	456 nm
		max.	460 nm
Spectral bandwidth at 50% I _{rel,max}	Δλ	typ.	23 nm
Viewing angle at 50% ${\rm I_v}$	2φ	typ.	120 °
Radiating surface	A _{color}	typ.	2.6 x 1.55 mm ²
Partial Flux acc. CIE 127:2007 4)	Φ _{Ε/V, 120°}	typ.	0.77
I _F = 6000 mA			
Forward Voltage ⁵⁾	V _F	min.	6.4 V
I _F = 6000 mA	· ·	typ.	7.0 V
		max.	7.6 V
Reverse voltage (ESD device)	$V_{R ESD}$	min.	45 V
Reverse voltage 2)	V _R	max.	1.2 V
I _R = 20 mA			
Real thermal resistance junction/board	$R_{thJB real}$	typ.	1.1 K / W
Electrical thermal resistance junction/board with efficiency $\eta_{\rm e}$ = 31 %	$R_{thJB elec.}$	typ.	0.76 K / W

OS-IN-2021-008-A



Brightness Groups

Group	Total radiant flux ¹⁾ $I_F = 6000 \text{ mA}$ min. Φ_e	Total radiant flux ¹⁾ $I_{F} = 6000 \text{ mA}$ max. Φ_{e}
FP	11200 mW	12100 mW
FQ	12100 mW	13000 mW
FR	13000 mW	14000 mW
FS	14000 mW	15000 mW
FT	15000 mW	16400 mW

Wavelength Groups

Group Dominant Wavelength ³⁾		Dominant Wavelength ³⁾
	min.	max.
	λ_{dom}	λ_{dom}
2	452 nm	456 nm
3	456 nm	460 nm


Group Name on Label

Example: FP-2	
Brightness	Wavelength
FP	2




Relative Spectral Emission⁴⁾

 $E_{rel} = f(\lambda); I_{F} = 6000 \text{ mA}; T_{J} = 25 \text{ }^{\circ}\text{C}$



Radiation Characteristics⁴⁾


 $I_{rel} = f(\phi); T_J = 25 \ ^{\circ}C$





Relative Partial Flux⁴⁾


 $\Phi_{_{\rm E}}(2\phi)/\Phi_{_{\rm E}}(180^\circ) = f(\phi); T_{_{\rm J}} = 25 \ ^{\circ}{\rm C}$






Forward current ⁴)

 $I_F = f(V_F); T_J = 25 \ ^{\circ}C$



Relative Radiant Power 4), 6)

 $\Phi_{_{\rm E}}/\Phi_{_{\rm E}}(6000 \text{ mA}) = f(I_{_{\rm F}}); T_{_{\rm J}} = 25 \text{ }^{\circ}\text{C}$




Dominant Wavelength⁴⁾

 $\Delta \lambda_{dom} = f(I_F); T_J = 25 °C$




Forward Voltage ⁴⁾

 $\Delta V_{_{\rm F}} = V_{_{\rm F}} - V_{_{\rm F}}(25 \ ^{\circ}{\rm C}) = f(T_{_{\rm J}}); I_{_{\rm F}} = 6000 \text{ mA}$




Relative Radiant Power⁴⁾

 $\Phi_{E}/\Phi_{E}(25 \text{ °C}) = f(T_{i}); I_{E} = 6000 \text{ mA}$




Dominant Wavelength ⁴⁾

 $\Delta \lambda_{dom} = \lambda_{dom} - \lambda_{dom} (25 \text{ °C}) = f(T_j); I_F = 6000 \text{ mA}$ $\Delta \lambda_{dom} / \text{ nm} \begin{array}{c} 10 \\ 8 \\ 6 \\ 4 \\ 2 \\ 0 \end{array}$






Dimensional Drawing 7)



Further Information:

Approximate Weight:	5,000.0 mg
ESD advice:	The device is protected by ESD device which is connected in parallel to the Chip.
Notes:	For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for any kind of wet cleaning or ultrasonic cleaning.
Connector:	Molex Pico-SPOX™ Wire-to-Board Header, Part Number 87438-1043
Recommended mating connector:	Molex Pico-SPOX™ Wire-to-Board Housing, Part Number 87439-1000 Crimp Terminal, Part Number 87421-0000






Pins 1: Substrate potential, isolated from Cathode and Anode Pins 2: Anode Pins 3: Cathode



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E



Profile Feature	Symbol	nbol Pb-Free (SnAgCu) Assembly		Unit	
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat ^{*)} 25 °C to 150 °C			2	3	K/s
Time t _s T _{smin} to T _{smax}	t _s	60	100	120	S
Ramp-up rate to peak ^{*)} $T_{\rm Smax}$ to $T_{\rm P}$			2	3	K/s
Liquidus temperature	TL		217		°C
Time above liquidus temperature	t		80	100	S
Peak temperature	Τ _Ρ		245	260	°C
Time within 5 °C of the specified peak temperature T_P - 5 K	t _P	10	20	30	S
Ramp-down rate* T _P to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S


All temperatures refer to the center of the package, measured on the top of the component

* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range



Tray 7)


38 pieces per Tray




C63062-A4389-B10-01



Barcode-Product-Label (BPL)




Barcode-Tray-Label (BTL)



OSRAM Opto Semiconductors

Schematic Transportation Box 7)



Dimensions of Transportation Box

Width	Length	Height	
333 ± 5 mm	218 ±5 mm	28 ± 5 mm	
337 ± 5 mm	218 ±5 mm	63 ± 5 mm	




Data Matrix Code Description

The Data Matrix Code bin information is Laser marked during testing Content: aaaa@bbbbb@cccc@ddddd@eeeee Data Matrix Code Type: ECC200

a = Luminous Flux (Phiv) [Im] or Radiant Flux (Phie) [W]	(example: 3306)
b = Forward Voltage (Vf) [V]	(example: 3.46)
c = Wavelength (Ldom) [nm]	(example: 618)
d = Color Coordinate Cx	(example: 0.321)
e = Color Coordinate Cy	(example: 0.641)
@: Seperator = Blank	

Type Designation System





Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- ¹⁾ Brightness: Brightness values are measured during a pulse train of 100 ms with a pulse width of 250 µs and a frequencey of 1 kHz, with an internal reproducibility of +/- 8 % and an expanded uncertainty of +/- 11 % (acc. to GUM with a coverage factor of k = 3). The peak brightness is calculated according to the pulse duration and frequency.
- ²⁾ Reverse Operation: This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- ³⁾ **Wavelength:** The wavelength is measured during a pulse train of 100 ms with a pulse width of 250 μ s and a frequencey of 1 kHz, with an internal reproducibility of ± 0,5 nm and an expanded uncertainty of ± 1 nm (acc. to GUM with a coverage factor of k=3).
- ⁴⁾ Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ⁵⁾ **Forward Voltage:** The forward voltage is measured during a pulse of typical 250 μs, with an internal reproducibility of +/- 0,05 V and an expanded uncertainty of +/- 0,1 V (acc. to GUM with a coverage factor of k=3).
- ⁶⁾ **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- ⁷⁾ **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.



Revisior	Revision History		
Version	Date	Change	
1.0	2019-09-18	Initial Version	
1.1	2019-10-10	Characteristics	
1.2	2020-02-18	Maximum Ratings Characteristics	
1.2	2020-02-18	Maximum Ratings Characteristics	
1.3	2021-03-19	Characteristics Ordering Information Brightness Groups Dimensional Drawing Maximum Ratings	

LE B P1MQ

Published by OSRAM Opto Semiconductors GmbHEU RoHS and China RoHS compliant productLeibnizstraße 4, D-93055 RegensburgEU RoHS and China RoHS compliant productwww.osram-os.com © All Rights Reserved.此产品符合欧盟 RoHS 指令的要求;

按照中国的相关法规和标准,不含有毒有害物质或元素。



e