

physical. chemical. biological.











HYT 939

Digital Humidity and Temperature Module Optimal for highly sophisticated, industrial applications


Benefits & Characteristics

- Calibrated and temperature compensated
- High chemical resistance
- Wide humidity and temperature range
- Very stable at high humidity
- Mechanically robust

- Excellent humidity/temperature accuracy and stability
- I²C protocol (address 0x28 or alternative address)
- Very low drift
- Interchangeable without adjustments
- Pressure-resistant version up to 16 bar upon request

Illustration¹⁾







Technical Data

Operating temperature range:	-40 °C to +125 °C
Operating humidity range:	0 % RH to 100 % RH
Hysteresis:	< ±1 % RH
Linearity error:	< ±1 % RH
Temperature error:	0.05 % RH/K (0 °C to +60 °C)
Operating voltage:	2.7 V to 5.5 V
Current consumption (nominal):	< 22 μA at 1 Hz measuring rate; 850 μA max.
Current consumption (sleep):	< 1 μΑ
Digital interface:	I ² C, address 0x28 or alternative address
Operating voltage (limits):	-0.3 V to 6 V
Storage conditions:	-20 °C to +50 °C

	Humidity	Temperature
Accuracy:	±1.8 % RH at +23 °C (0 % RH to 90 % RH)	±0.2 K (0 °C to +60 °C)
Reproducibility:	±0.2 % RH	±0.1 K
Resolution:	0.02 % RH	0.015 °C
Response time t ₆₃ :	< 10 s with metal mesh filter	< 10 s with metal mesh filter
Long-term drift:	< 0.5 % RH/a (at +23 °C and 30 % RH to 70 % RH - laboratory conditions)	< 0.05 K/a
Measuring principle:	Capacitive polymer humidity sensor	PTAT (integrated)

¹⁾ For actual size, see mechanical dimensions



physical. chemical. biological.














Product image



Mechanical Dimensions - HYT 939



Mechanical Dimensions - HYT 939p





physical. chemical. biological.
















1	2	3	4
SCL	VCC	GND	SDA

Order Information

	HYT 939
Order code	103922
Former order code	150.00067

Order Information - Pressure-tight up to 16 bar

	HYT 939p
Order code	103941
Former oder code	150.00096

Additional Electronics

	Document name:
LabKit:	DHHYTLabKit_E

Additional Documents

	Document name:
Application Note:	AHHYTM_E



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com