



MADE
IN THE **USA**
PATENTED

Product Description:

- Semi-Recessed PPE Dispensing System
- Holds a variety of gowns, three boxes of gloves, one box of earloop-style face masks, one box of shield-style face masks, and built-in storage area (for a variety of medical supplies, fourth box of gloves, or one box of N-95 face masks)
- Low profile
- Slotted keyless cam lock (one key included, extras sold separately)
- Screw holes in sides to mount to stud framing in wall
- Made of Quartz Beige Powder-Coated Steel

Primary Area for Product Usage:

- All patient care areas requiring personal protective equipment and isolation supplies

Dispenses:

- Top left section: Gowns (up to 15 flat pack, 15 launderable, or 2 blue boxes) folded up to 14.94"W x 14.50"H x 4.06"D (37.8 cm x 36.8 cm x 10.9 cm)
- Top right section: One box shield-style face masks up to 8.38"W x 9.50"H x 4.06"D (21.1 cm x 23.9 cm x 10.4 cm)
- Middle right section: One box earloop-style face masks up to 8.38"W x 4.75"H x 4.06"D (20.6 cm x 12.2 cm x 10.4 cm)
- Two top glove sections: Two boxes of gloves up to 11.63"W x 6.25"H x 4.06"D (29.5 cm x 15.9 cm x 10.4 cm)
- Two bottom sections: Two boxes of gloves up to 11.63"W x 5.50"H x 4.06"D (29.5 cm x 14.0 cm x 10.4 cm), or one box of gloves and miscellaneous medical supplies in bottom right

Package Specifications:

- Package Quantity: 1 per case
- 27"L x 8"W x 32"H (68.6 cm x 20.3 cm x 81.3 cm)
- 26.0 lbs (11.8 kg) - approximated

Product Specifications (overall external dimensions):

- 24.36"W x 27.65"H x 4.77"D (61.9 cm x 70.2 cm x 12.1 cm)
- 22.4 lbs (10.1 kg) - approximated


Accessories (each sold separately):

- MP-047: Clip-On Sign Holder (shown attached below)
- REK01-0320: Recessed Key



Mounting Specifications:

- Installation should be performed only by a licensed contractor.






Installation


Always mount dispensers securely *prior* to loading with product.

- Door can be locked or unlocked using a small flat object, such as a coin, or similar rounded edge.



1

- Door can be removed by squeezing and turning posts on hinges as shown.



2

Parts included:

- Dispenser

Tools Required:

- No tools required to assemble dispenser

Characteristics & Care

Powder-Coated Steel

Material Characteristics

Designed for Long-Term Use

Our steel dispensers and stands are coated with polyester powders which makes them highly resistant to corrosion.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting because it is impact resistant and is not effected by extremes in temperature.

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service.

Care and Cleaning

For best results, clean by washing the surface with a diluted solution of a mild, non-abrasive detergent in cold or warm water and a non-abrasive cloth. Standard hospital cleaning supplies can be used.

Dry with a soft cloth. Do not use any solvent-based materials, abrasives (e.g. Scotch-brite, steel wool), or apply excessive force during cleaning.