



Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions:

Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith. See the Menda Terms and Conditions - Mendapump.com/Terms-And-Conditions.aspx

One-Touch Pump:

- "One-Touch" one-handed operation frees operator's hands for use
- Precision machined valves for smooth consistent operation
- Recommended for one-handed dispensing of liquids, solvents, and chemicals
- Stainless-steel construction No silicone or latex suitable for ultra clean environments
- · Cam-lock hinge keeps lid open and closed, reduces odors
- · Compatible with any 38-400 threaded neck container
- · Dispenses approximately 0.2cc of liquid with each pump

Pump Material Stainless-Steel

Locks for Travel No

Neck Size / Thread 38-400

Lid-Type Cam-lock hinge lid

Gasket Material LDPE

Pump Care:

Some types of fluids may leave a residue in the mechanism of the dispenser. Over time, this can reduce the performance of the pump.

Occasional cleaning is recommended to maintain your unit to original efficiency.

Clean by flushing the mechanism thoroughly with warm soapy water. Flush the mechanism again with clean water to remove any soap residue. Do not boil or steam the dispenser. For long periods of inactivity, pumps should be flushed free of liquid and stored inverted in a dry place.

Specifications and procedures subject to change without notice. Unless otherwise noted, tolerance is ±10%.

ONE-TOUCH, PUMP ONLY, NO STEM

3651 WALNUT AVE., CHINO, CA 91710

PHONE: (909) 627-2453 WEBSITE: MendaPump.com DRAWING NUMBER 35300

DATE: Aug. 2016

MENDA