

**Data sheet | Item number: 211-813**

Nozzles; Length: 12 mm; For the use of 211-811; halogen-free; Cable outer diameter: 5.0 ... 11.0 mm; transparent

[www.wago.com/211-813](http://www.wago.com/211-813)



**Data**

**Technical data**

Suitable	for wire diameter 5 ... 11 mm
Delivery form	Component
Properties	for one 211-811 marker
Printing device	Smart Printer (Thermal Transfer Printer)

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



## Physical data

Length	12 mm
Sheathed cable diameter	5 ... 11 mm

## Mechanical Data

Mounting type	Sliding on conductor
---------------	----------------------

## Material Data

Color	transparent
Material	Polyurethane
Adhesive information	without adhesive
Halogen-free	Yes
Weight	0.5 g

## Environmental requirements

Ambient temperature (storage)	+5 ... +40 °C
Ambient temperature (operation)	-40 ... +80 °C
Relative humidity	40 ... 80 %

## Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	500 pcs
Packaging type	box
Country of origin	IT
GTIN	4050821674993
Customs tariff number	39269097900

## Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Subject to changes. Please also observe the further product documentation!



## Required accessories

### Marking accessories

Marker

Item no.: 211-811

Marker; for Smart Printer; for use in nozzles; Length: 12 mm; white

[www.wago.com/211-811](http://www.wago.com/211-811)

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 211-813

URL

Download

Nozzles; Length: 12 mm; For the use of 211-811; halogen-free; Cable outer diameter: 5.0 ...11.0 mm; transparent

## Installation Notes

### Application



Slide the marker into the marking sleeve receptacle. Replacing the marker is also possible after the conductor has been terminated.

### Application

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



Compress the sleeve and slide it onto the conductor to be marked.

Subject to changes. Please also observe the further product documentation!