

# **GL010–0223** BOWMAN<sup>®</sup> *Signature Series* – Glove Box Dispenser – Single



### Related Products (each sold separately):

GL010-0233: BOWMAN® Signature Series - Glove Box Dispenser - Cherry Fauxwood (shown below)



### **Product Description:**

- Glove Box Dispenser Single
- Holds one box of gloves
- Three-way keyholes for vertical or horizontal wall mounting
- BOWMAN® Signature Series Maple Fauxwood ABS Plastic

### Primary Area for Product Usage:

Anywhere gloves are needed

#### Dispenses:

- Box(es) no larger than 5.50"W x 10.00"H x 3.75"D (14.0 cm x 25.4 cm x 9.5 cm)
- Box(es) no smaller than 4.50"W x 9.00"H x 3.00"D (11.4 cm x 22.9 cm x 7.6 cm)


#### Package Specifications:

- Package Quantity: 12 per case
- 18"L x 16"W x 10"H (45.7 cm x 40.6 cm x 25.4 cm)
- 11.0 lbs (5.0 kg) approximated

**Product Specifications** (overall external dimensions):

- 5.75"W x 10.13"H x 4.00"D (14.6 cm x 25.7 cm x 10.2 cm)
- 0.8 lbs (0.4 kg) approximated

**Mounting Specifications:** 






## GLO10-0223 BOWMAN<sup>®</sup> Signature Series - Glove Box Dispenser - Single Installation Instructions/Characteristics & Care

## Installation

Always mount dispensers securely *prior* to loading with product.



• Mount securely to a wall with screws approved and supplied by building maintenance.

2

### Parts included:

• Dispenser

### **Tools Required:**

No tools required to assemble dispenser

Care and Construction Fauxwood ABS Plastic

## **Material Characteristics**

Designed for Long-Term, Heavy-Duty Applications

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness. The fauxwood finish is ARVINYL laminate created from a semi-rigid film.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. To ensure product longevity, fauxwood products should not be mounted in very hot or cold areas.

### Care and Cleaning

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.

GL010-0223 - Installation/Characteristics & Care

Information subject to change without notice. Dimensions are approximate. (Not to scale) 800.962.4660 • www.BowmanDis ©2019 BOWMAN® Manufacturing Company, Inc. All Rights Reserved. Product specifications subject to change without notification. Consumables not included. GL0100223TDSa

BOWMAN Dispensers 20325 71st Ave NE, Suite D, Arlington, WA 98223 800.962.4660 • www.BowmanDispensers.com