

1/2" Flow Meter

Reads Total flow and flow rate

Range **5.7 L/min – 75.70 L/min**

Accuracy **+/- 10%**

Connector Tinned leads

Thread 1/2" Female NPT

Max pressure 100 PSI


Temperature range °C -29 - 82 °C

Max viscosity 200 SSU


Cable length **69cm (27.1")**

Voltage **4.0V – 24 VDC**

Life expectancy ~10 years








Wiring

The Atlas Scientific 1/2" Flow Meter has a 69cm (27.1") cable that terminates with three tinned leads; Red (VCC), White (Pulse), and Black (Ground).



Specifications

Data output Square wave
Max pressure 100 PSI


Max viscosity
Cable length

69 cm

Weight 104.3 grams

Food Safe
Gasoline Safe
Ves
Diesel Safe
Ves
Kerosene Safe
Yes


NSF/ANSI 61 Compliant





Operating principle


Paddle wheel flow meters like the Atlas Scientific 1/2" Flow Meter use frequency to calculate water flow. As water passes through the flow meter, the magnetic rotor spins at a rate proportional to the flow, producing a frequency. The relationship between water frequency and volume is not linear; an equation to convert the frequency to volume is found at the end of this document.



This flow meter is intended for medium-to-high flow ranges from 5.7 L/min (1.5GPM) up to 75.70 L/min (20 GPM).

Pre-filter requirements


If water with particulate matter will be passing through the flow meter, a pre-filter of at least **80 microns** must be used. Without the use of a pre-filter, the turbine blades can become jammed. Jammed turbine blades will not damage the flow meter; however, it will not be possible to get accurate flow readings until the blockage has been cleared.




Laminar flow

Laminar flow can be thought of as the opposite of turbulent flow. In order for the flow meter to work properly, the liquid entering the flow meter should have a streamlined laminar flow. Achieving laminar flow is not hard to do; simply allow for 20cm (8") of straight pipe just before the liquid enters the flow meter.


Turbulent fluid entering the flow meter can cause inaccuracies in flow rate monitoring.



Laminar flow




Turbulent flow




Liquid exiting the flow meter

Liquid should not be permitted to simply fall out of the flow meter. This would let air ente the flow meter and lead to inaccurate readings.




FOR ACCURATE READINGS, YOU CANNOT HAVE AIR IN THE LINE.





Low flow adapter


To monitor flow rates <15L/Min, use the low flow adapter included with the flow meter. Using the low flow adapter will limit your max flow rate to 45L/ min



A low flow adapter is included with the Atlas Scientific 1/2" Flow Meter.

Data output

The white lead from the 1/2" Flow Meter will output a square wave frequency from 0 - 200 + Hz. The amplitude of the frequency will always equal the VCC. A single pulse is a rising edge followed by a falling edge.



The amount of liquid moving through the flow meter is quantified by the frequency that the flow meter outputs. This is known as the flow meters K-factor.




K-factor

As stated earlier, paddle wheel flow meters use frequency to calculate water flow. The relationship between frequency and volume is not linear. Here are the equations needed to calculate the volume.

1/2" Flow Meter with the low flow adapter installed

| GPM | LPM | Output Frequency – Hz | |
|-----|------|--------------------------|------------------------------|
| 1.5 | 5.7 | 17 | |
| 2 | 7.6 | 25.9 | |
| 2.5 | 9.5 | 34 | |
| 3 | 11.4 | 43 | |
| 4 | 15.2 | 60 | |
| 5 | 19 | 76.6 | |
| 6 | 22.8 | 94 | LPM = 0.2152 x [Hz] + 2.2928 |
| 7 | 26.6 | 111 | |
| 8 | 30.4 | 129 | |
| 9 | 34.2 | 147 | |
| 10 | 38 | 165 | |
| | 41.8 | 185 | |
| 12 | 45.6 | 204 | |



1/2" Flow Meter <u>without</u> the low flow adapter installed

| GPM | LPM | Output Frequency – Hz | |
|-----|------|--------------------------|------------------------------|
| 4 | 15.2 | 34 | |
| 5 | 19 | 44.8 | |
| 6 | 22.8 | 55 | |
| 7 | 26.6 | 65.9 | |
| 8 | 30.4 | 76 | |
| 9 | 34.2 | 87.5 | |
| 10 | 38 | 99 | |
| 11 | 41.8 | 110 | |
| 12 | 45.6 | 122 | LPM = 0.3256 x [Hz] + 5.2004 |
| 13 | 49.4 | 135 | |
| 14 | 53.2 | 147 | |
| 15 | 57 | 158 | |
| 16 | 60.8 | 170 | |
| 17 | 64.6 | 183 | |
| 18 | 68.4 | 195 | |
| 19 | 72.2 | 207 | |
| 20 | 76 | 220 | |
| | | | |