




## MOCC57-19-A

Ruland MOCC57-19-A, 19mm Oldham Coupling Hub, Aluminum, Clamp Style With Keyway, 57.2mm OD, 28.7mm Length





## **Description**

Ruland MOCC57-19-A is a clamp oldham coupling hub with a 19mm bore, 6mm keyway, 57.2mm OD, and 28.7mm length. It is a component of a three-piece design consisiting of two anodized aluminum hubs press fit onto a center disk. This three-piece design allows for a highly customizable coupling that easily combines clamp or set screw hubs with inch, metric, keyed, and keyless bores. Disks are available in three materials allowing the user to tailor coupling performance to their application. MOCC57-19-A can accommodate all forms of misalignment and is especially useful in applications with high parallel misalignment (up to 10% of the OD). It operates with low bearing loads protecting sensitive system components such as bearings and has a balanced design for reduced vibration at speeds up to 6,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MOCC57-19-A is machined from bar stock that is sourced exclusively from North American mills and is RoHS3 and REACH compliant. It is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

**Product Specifications** 

r roduct opecifications			
Bore (B1)	19 mm	Keyway (K)	6 mm
Outer Diameter (OD)	57.2 mm	B1 Max Shaft Penetration	28.7 mm
Bore Tolerance	+0.03 mm / -0.00 mm	Hub Width (LH)	28.70 mm
ength (L)	78.7 mm	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
orged Clamp Screw	M6	Number of Screws	1 ea
Screw Material	Alloy Steel	Screw Finish	Black Oxide
Seating Torque	16 Nm	Hex Wrench Size	5.0 mm
orque Specifications	Torque ratings vary with insert selection	Angular Misalignment	0.5°
Parallel Misalignment	0.010 in (0.25 mm)	Max Parallel Misalignment	0.225 in (5.72 mm)
xial Motion	0.008 in (0.20 mm)	Moment of Inertia	8.495 x 10 <sup>-5</sup> kg-m <sup>2</sup>
laximum Speed	4,500 RPM	Recommended Inserts	OD36/57-AT, OD36/57-PEK
ull Bearing Support Required?	Yes	Zero-Backlash?	Yes
alanced Design	Yes	Mechanical Fuse?	Yes
IPC	634529125908	Country of Origin	USA
laterial Specification	2024-T351 Aluminum Bar	Finish	Black Anodized
inish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize	Manufacturer	Ruland Manufacturing
emperature	Acetal Disk -10°F to 150°F (-23°C to 65°) Nylon Disk -10°F to 130°F (-23°C to 54°C) PEEK Disk -10°F to 300°F (-23°C to 148°C)	Weight (lbs)	0.399700
Tariff Code	8483.60.8000	UNSPC	31163015
lote 1	"Now available in stainless steel!"		
lote 2	"Performance ratings are for guidance only. The user must determine suitability for a particular application."		
Note 3	"Torque ratings for the couplings are based on the physical limitations/failure point of the torque disks. Unde normal/typical conditions the hubs are capable of holding up to the rated torque of the disks. Please consult technical support for more assistance."		

## Prop 65

▲ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>.

## **Installation Instructions**

- 1. Align the bores of the MOCC57-19-A oldham coupling hubs on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misalignment:* 0.5° *Parallel Misalignment:* 0.010 in (0.25 mm), *Axial Motion:* 0.008 in (0.20 mm))
- 2. Rotate the hubs on the shaft so the drive tenons are located 90° from each other.
- 3. Place a torque disk so one groove fits over the drive tenons of a hub and center the disk by hand.
- 4. Insert a shim with the thickness of the coupling's axial motion rating into the groove of the torque disk.
- 5. Slide the tenons of the second hub into the mating groove in the disk until it touches the shim stock.
- 6. Fully tighten the M6 screw(s) on each hub to the recommended seating torque of 16 Nm using a 5.0 mm hex torque wrench.
- 7. Remove the shim stock to leave a small gap between the top of the drive tenons and the torque disk to allow for axial movement.