SFH 3010

SMARTLED®

Silicon NPN Phototransistor (not for new design in automotive applications)







Applications

- Access Control (IRIS/Vein Scan, Face Recognition)
- Electronic Equipment

 Health Monitoring (Heart Rate Monitoring, Pulse Oximetry)

Features:

- Package: Epoxy, diffuse
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Very small package: (LxWxH) 1.7 mm x 0.8 mm x 0.65 mm
- Large viewing angle ± 80°
- Available on tape and reel
- Spectral range of sensitivity: (typ) 420 ... 1100 nm

Ordering Information

| Type | Photocurrent | Ordering Code |
|------------|---|---------------|
| | $V_{CE} = 5 \text{ V}; \lambda = 950 \text{ nm}; E_{e} = 0.5 \text{ mW/cm}^{2}$ | |
| | I _{PCE} | |
| SFH 3010-Z | ≥ 25 µA | Q65110A6458 |



| Maximum Ratings | ım Ratings |
|------------------------|------------|
|------------------------|------------|

| Τ. | = | 25 | $^{\circ}C$ |
|----|---|----|-------------|
| Ι, | _ | 20 | $^{\circ}$ |

| Parameter | Symbol | | Values |
|---|-----------------------|------|--------|
| Operating temperature | T _{op} | min. | -40 °C |
| | | max. | 100 °C |
| Storage temperature | T _{stg} | min. | -40 °C |
| | 9 | max. | 100 °C |
| Collector-emitter voltage | V _{CE} | max. | 15 V |
| Collector-emitter voltage pulse $t \le 10 \mu\text{s}; T_{\text{A}} = 25 ^{\circ}\text{C}$ | V _{CE pulse} | max. | 30 V |
| Collector current | I _c | max. | 15 mA |
| Collector surge current τ ≤ 10 μs | I _{cs} | max. | 75 mA |
| Emitter-collector voltage | V_{EC} | max. | 7 V |
| Total power dissipation | P _{tot} | max. | 130 mW |
| ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2) | V_{ESD} | max. | 2 kV |



Characteristics


 $T_A = 25 \,^{\circ}C$

| Parameter | Symbol | | Values |
|--|-----------------------------|--------------|------------------------|
| Wavelength of max sensitivity | $\lambda_{_{\text{S max}}}$ | typ. | 860 nm |
| Spectral range of sensitivity | λ _{10%} | typ. | 420 1100 nm |
| Dimensions of chip area | LxW | typ. | 0.38 x 0.38 mm x mm |
| Radiant sensitive area | А | typ. | 0.04 mm² |
| Half angle | φ | typ. | 80 ° |
| Dark current V _{CE} = 20 V; E = 0 | I _{CE0} | typ. max. | 1 nA 50 nA |
| Rise time $I_c = 1 \text{ mA}$; $V_{cc} = 5 \text{ V}$; $R_L = 1 \text{ k}\Omega$ | t _r | typ. | 7 µs |
| Fall time $I_c = 1 \text{ mA}$; $V_{cc} = 5 \text{ V}$; $R_L = 1 \text{ k}\Omega$ | t _f | typ. | 7 µs |
| Collector-emitter saturation voltage $^{1)}$ I _C = 10 μ A, E _e = 0.5 mW / cm ² , λ = 950 nm | V _{CEsat} | typ. | 140 mV |
| Capacitance $V_{CE} = 0 \text{ V}; f = 1 \text{ MHz}; E = 0$ | C _{CE} | typ. | 1.3 pF |
| Thermal resistance junction ambient real | R_{thJA} | max. | 450 K / W |
| Thermal resistance junction solder point real | R_{thJS} | max. | 250 K / W |




Relative Spectral Sensitivity 2), 3)

$$S_{rel} = f(\lambda)$$




Directional Characteristics 2), 3)

$$S_{rel} = f(\phi)$$




Photocurrent 2), 3)

$$I_{PCE} = f(V_{CE}); E_{e} = Parameter$$




Dark Current 2), 3)

$$I_{CE0} = f(V_{CE}); E = 0;$$




Collector-Emitter Capacitance 2), 3)

$$C_{CE} = f(V_{CE}); f = 1 MHz; E = 0$$




Dark Current 2)

$$I_{CE0} = f(T_A); V_{CE} = 20 V; E = 0$$




Photocurrent 2)

$$I_{PCE,rel} = f(T_A); V_{CE} = 5 V$$




Power Consumption


$$P_{tot} = f(T_A)$$





Dimensional Drawing 4)





GPLY7036


Further Information

Approximate Weight: 2.1 mg


Package marking: Collector



Recommended Solder Pad 4)




Recommended Solder Pad 4)





Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




| Profile Feature | Symbol | Pb | -Free (SnAgCu) Ass | sembly | Unit |
|---|--------------------------------|---------|--------------------|---------|------|
| | | Minimum | Recommendation | Maximum | |
| Ramp-up rate to preheat*) | | | 2 | 3 | K/s |
| 25 °C to 150 °C | | | | | |
| Time t _s | t_s | 60 | 100 | 120 | S |
| T_{Smin} to T_{Smax} | | | | | |
| Ramp-up rate to peak*) | | | 2 | 3 | K/s |
| T_{Smax} to T_{P} | | | | | |
| Liquidus temperature | T_L | | 217 | | °C |
| Time above liquidus temperature | $t_{\scriptscriptstyle \perp}$ | | 80 | 100 | S |
| Peak temperature | T_{P} | | 245 | 260 | °C |
| Time within 5 °C of the specified peak temperature T _P - 5 K | t _P | 10 | 20 | 30 | S |
| Ramp-down rate* T _P to 100 °C | | | 3 | 6 | K/s |
| Time 25 °C to T _P | | | | 480 | S |

All temperatures refer to the center of the package, measured on the top of the component



^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range


Taping 4)



OHAY1491




Tape and Reel 5)




Reel Dimensions

| Α | W | N_{\min} | W_1 | $W_{2\mathrm{max}}$ | Pieces per PU |
|--------|--------------------|------------|------------|---------------------|---------------|
| 180 mm | 8 + 0.3 / - 0.1 mm | 60 mm | 8.4 + 2 mm | 14.4 mm | 5000 |

Barcode-Product-Label (BPL)




Dry Packing Process and Materials 4)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Schematic Transportation Box 4)



Dimensions of Transportation Box

| Width | Length | Height |
|------------|------------|-----------|
| 200 ± 5 mm | 195 ± 5 mm | 30 ± 5 mm |

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- 1) **IPCEmin:** IPCEmin is the min. photocurrent of the specified group.
- Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ³⁾ **Testing temperature:** TA = 25°C (unless otherwise specified)
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁵⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



| Revision | n History | |
|----------|------------|--------------|
| Version | Date | Change |
| 1.3 | 2019-07-15 | Discontinued |



Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。



