
SPECIFICATION CONTROL DRAWING



MATERIAL

1. DUMMY PLUG: Beryllium Copper. Plating: see below.

APPLICATION


1. A Dummy Plug is designed to replace a HET-A-*** ferrule where applicable and is purchased separately from the

originalHexashield Adaptor assembly.

INSTALLATION

- The Dummy Plug replaces the HET-A-*** as shown in the Installation Procedure RPIP-696-04.

Part Numbering:



300 Const		tronics Corporation titution Drive, rk, CA. 94025, U.S.A.		DUMMY PLUG FOR HEXASHIELD ADAPTORS						
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]						DOCUMENT NO.: HEX07-AB/-AC				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ROU	GLES: N/A IGHNESS IN RON	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.			DOC. ISSUE: DATE			TE: 5-Nov-03	
DRAWN BY: M. FOROND	Α	CAGE CODE 06090		REPLACES: R010433	DCR NUMBER: D030543	PROD. REV.:	SCALE: None	SIZE:	SHEET: 1 of 1	