

Features:



- Dissipative bottles are made to protect ESD sensitive items, charges removed when grounded.
- Low-Charging, and will charge decay ± 1000 volts to ± 100 volts in less than 2 seconds.
- Available with 3 different needle sizes.
- Made in America for superior quality

Specifications:

Volume Resistance

 1×10^9 to < 1×10^{11} ohms tested per ANSI/ESD STM11.12

Item	Description
35291	Dissipative Flux Dispenser, 2 oz (60mL), 26 GA (0.24mm ID) Needle
35292	Dissipative Flux Dispenser, 2 oz (60mL), 20 GA (0.58mm ID) Needle
35293	Dissipative Flux Dispenser, 2 oz (60mL), 16 GA (1.2mm ID) Needle

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20-2008 section 2.4 Sources of Static Electricity]



Unless otherwise noted, tolerance ± 10%

Specifications and procedures subject to change without notice.

Blue Dissipative Flux Dispensers

3651 WALNUT AVE., CHINO, CA 91710 PHONE: (909) 627-2453 • FAX: (909) 755-8848

DRAWING NUMBER 35291

DATE: August 2013

MENDA

WEBSITE: MendaPump.com