

## **Trizact<sup>™</sup> Diamond Tile 677XA**

<b>Technical Data Sheet</b>	September 200
Product Description	A structured, fixed abrasive composite pad consisting of an inorganic abrasive (vitreous diamond agglomerates) in an organic binder (cross-linked polymer) capable of lapping a multitude of substrates on varied equipment and processes.
Key Features	<ul> <li>Eliminates messy slurries</li> <li>Produces superior surface finish to slurry</li> <li>Reduces overall process time</li> <li>Reduces waste disposal costs</li> <li>Eliminates lap plate replacement</li> <li>Fits on any lapping machine</li> </ul>
Grades and Sizes	<ul> <li>Available in 3, 6 and 9 micron grades and includes PSA backing.</li> <li>Manufactured to any shape, with any hole size and hole configuration.</li> <li>For discs or sheets smaller than 9", specify 3M™ Trizact™ Diamond Tile 677XA</li> <li>For discs or sheets greater than 9", specify 3M™ Trizact™ Diamond Tile 677XA Type PC Polycarbonate backing adds rigidity to larger discs.</li> <li>For discs or sheets greater than 9" and less than 47", 3M™ Trizact™ Diamond Tile 677XA Type PC pads will come in one piece.</li> <li>For discs or sheets greater than 47", 3M™ Trizact™ Diamond Tile 677XA Type PC pads will come in four pieces.</li> </ul>
Grade Selection	Grade selection is based on material type and process requirements. The smallest micron grade that will give stable cut rate for a given material is recommended. Using the smalles possible micron grade will result in a finer rough lap finish, reducing polish time by up to 50%.
Equipment	Trizact™ Diamond Tile 677XA is designed to work with double and single sided lapping machines and can be directly mounted on most plate material types or geometry.
Directions for Use	Reference the following Technical Application Bulletins for detailed information on use of Trizact™ Diamond Tile 677XA:  — Machine Prep and Pad Mounting Instructions  — Lubricant Use and Filtering Instructions  — Pad Conditioning Instructions  — Frequently Asked Questions

## Typical Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Average Material Removal and Finish						
Grade	Borofloat™ Glass	Pyrex® Glass	BK7 Glass	Fused Quartz	Window Glass	
3 micron	58 μm/min Ra = 1575 Å Rt = 1.408 μm	55 $\mu$ m/min $Ra = 1625 \text{ Å}$ $Rt = 1.545 \mu$ m	22 $\mu$ m/min $Ra = 1629 \text{ Å}$ $Rt = 1.455 \mu$ m	58 $\mu$ m/min $Ra = 657 \text{ Å}$ $Rt = 0.6437 \mu m$	n/a	
6 micron	105 $\mu$ m/min $Ra = 2352 \text{ Å}$ $Rt = 2.169 \mu$ m	115 $\mu$ m/min $Ra = 2495 \text{ Å}$ $Rt = 2.316 \mu$ m	76 $\mu$ m/min $Ra = 2531 \text{ Å}$ $Rt = 2.284 \mu m$	69 $\mu$ m/min $Ra = 951 \text{ Å}$ $Rt = 0.9865 \mu$ m	43 $\mu$ m/min** $Ra = 2814 \text{ Å}$ $Rt = 2.503 \mu$ m	
9 micron	181 $\mu$ m/min $Ra = 3035 \text{ Å}$ $Rt = 2.580 \mu$ m	165 $\mu$ m/min $Ra = 3152 \text{ Å}$ $Rt = 2.827 \mu$ m	105 $\mu$ m/min $Ra = 3842 \text{ Å}$ $Rt = 3.429 \mu$ m	89 $\mu$ m/min $Ra = 1336 \text{ Å}$ $Rt = 1.0792 \mu m$	72 $\mu$ m/min** $Ra = 3499 \text{ Å}$ $Rt = 3.061 \mu$ m	

Double sided lapping on Peter Wolters AC 500 machine.

## Storage

Pads should be stored flat, in a clean environment. Stacking up to 8 pads, or pad segments, is acceptable. Do not store pads on edge.

**FOR ADDITIONAL INFORMATION:** To request additional product information or to arrange for sales assistance, call 1-800-251-8634. Address correspondence to: 3M Industrial Business Customer Response Center, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55106. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

**PRODUCT USE:** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

WARRANTY AND LIMITED REMEDY: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

**LIMITATION OF LIABILITY:** Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence, or strict liability.

Borofloat is a trademark of Schott Corporation. Pyrex is a registered trademark of Corning Inc. Sabrelube is a registered trademark of Chemetall Oakite. 3M and Trizact are trademarks of 3M.



## **Industrial Business**

Electronics Markets Materials Division 3M Center, Building 225-3N-11 St. Paul, MN 55144-1000 phone: 1-800-251-8634 or 1-651-736-3068 www.3M.com/electronicmaterials



<sup>2</sup> psi, 96 rpm, 200 ml/min flow rate, 5% Sabrelube\* 9016 in water

<sup>5</sup> minute cycles, ten 65mm diameter substrates

<sup>\*</sup> Data is an average of four 1.1mm scans with a  $0.25\mu m$  tip radius and 250  $\mu m$  cut off

<sup>\*\* 10%</sup> Sabrelube® 9016 in water