

Shrink sleeve - WMS 2,4 (EX4)R BK - 0800415

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, black, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK ROLL X1, Unperforated, Mounting type: slide on, Cable diameter: 0.8-2.4 mm, Lettering field: 4 x 30000 mm

The figure shows the WMS 12,7 (Ex20)R BK version

Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- UL 224 (125°C, 600 V, all tubing)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- Individual markers can be cut to any length up to 1 m

Key commercial data

| | |
|--------------------------------------|-----------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 184.2 GRM |
| Custom tariff number | 39173200 |
| Country of origin | China |

Technical data

Dimensions

| | |
|------------|------|
| Length (b) | 30 m |
| Width (a) | 4 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -55 °C ... 135 °C |
|---------------------------------|-------------------|

General

| | |
|-----------------------|--------------|
| Color | black |
| Base element material | polyolefine |
| Components | Halogen-free |
| Material | Polyolefine |

Shrink sleeve - WMS 2,4 (EX4)R BK - 0800415

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 1000 |
| Number of individual labels per row | 1 |
| Marking mounting type | slide on |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27400401 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001530 |
| ETIM 4.0 | EC000217 |
| ETIM 5.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |