

Data sheet | Item number: 211-812

Nozzles; Length: 12 mm; For the use of 211-811; halogen-free; Cable outer diameter: 1.4 ... 5.0 mm; transparent

www.wago.com/211-812



Data

Technical data

Suitable	for wire diameter 1.4 ... 5 mm
Delivery form	Component
Properties	for one 211-811 marker
Printing device	Smart Printer (Thermal Transfer Printer)

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Physical data

Length	12 mm
Sheathed cable diameter	1.4 ... 5 mm

Mechanical Data

Mounting type	Sliding on conductor
---------------	----------------------

Material Data

Color	transparent
Material	Polyurethane
Adhesive information	without adhesive
Halogen-free	Yes
Weight	0.2 g

Environmental requirements

Ambient temperature (storage)	+5 ... +40 °C
Ambient temperature (operation)	-40 ... +80 °C
Relative humidity	40 ... 80 %

Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 8.0	EC001530
ETIM 7.0	EC001530
PU (SPU)	500 pcs
Packaging type	box
Country of origin	IT
GTIN	4050821674986
Customs tariff number	39269097900

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Subject to changes. Please also observe the further product documentation!

Required accessories

Marking accessories

Marker

Item no.: 211-811

Marker; for Smart Printer; for use in nozzles; Length: 12 mm; white

www.wago.com/211-811

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-812

URL

Download

Nozzles; Length: 12 mm; For the use of 211-811; halogen-free; Cable outer diameter: 1.4 ... 5.0 mm; transparent

Installation Notes

Application



Slide the marker into the marking sleeve receptacle. Replacing the marker is also possible after the conductor has been terminated.

Application

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



Compress the sleeve and slide it onto the conductor to be marked.

Subject to changes. Please also observe the further product documentation!